## **MegaVision Water Solutions**



## Flat Sheet MF02



MEGAVISION<sup>®</sup> Flat Sheet MF02 membrane is a HYPER™ polyvinylidene fluoride (PVDF) ultrafiltration membrane with a nominal pore size of 0.2 micron. MF02 membrane sheet is available in dry flat sheet rolls.

## **Membrane Specifications**

Membrane Chemistry	Backing Material	Nominal Pore Size (μm)
Polyvinylidene Fluoride (PVDF)	Non-Woven Polyester (120 g/m²)	0.2

Permeability <sup>a</sup> LMH/bar (GFD/psi)	Thickness (µm)	WCO %	pH Range	Chlorine Tolerance <sup>b</sup>
>700 (>28.4)	280~285	48 ±5	1 ~ 12	1,000 ppm at pH ≥ 10.5

a Test conditions: Clean water, 1 bar (14.5 psi), 20°C (68°F). Membrane specifications may change without notice as design revisions occur.

## **Important Information**

Standard Sizes : MegaVision flat sheet membrane is available in a sample size of 520 mm x 1,016 mm (20

in x 40 in) and in a nominal roll size of 250 m x 1,016 mm (820 ft x 40 in). Custom lengths

may be available on request.

Initial Flush: MegaVision recommends flushing membrane for 30 minutes and discarding permeate

during the flush prior to operation.

Storage: Membrane shipped dry should be stored away from direct sunlight in a cool, dry place.

Please see Membrane Storage Guide.

The information and data contained herein are deemed to be accurate and reliable and are offered in good faith, but without guarantee of performance. MegaVision membrane assumes no liability for results obtained or damages incurred through the application of the information contained herein. Customer is responsible for determining whether the products and information presented herein are appropriate for the customer's use and for ensuring that customer's workplace and disposal practices are in compliance with applicable laws and other governmental enactments. Specifications subject to change without notice. MegaVision Membrane is registered brand of Shanghai MegaVision Membrane Technology & Engineering Co. Ltd. All rights reserved © 2019.



b Tolerance listed for periodic, short-term cleanings in wastewater applications.